

AE 4090**Hinweis zum mitgelieferten Mikrofon**

Sehr geehrter Kunde,
entgegen den Angaben in der Bedienungsanleitung finden Sie in dieser Verpackung ein geändertes Mikrofon für Ihr AE 4090 vor.
Wir haben damit auf die Wünsche vieler CB Funker reagiert, die ein etwas grösseres und bess in der Hand liegendes Mikrofon bevorzugen.
Gleichzeitig haben wir noch die akustischen Eigenschaften verbessert:
Das neue Mikrofon ist unempfindlicher gegenüber Wind- und Atemgeräuschen und bringt mehr Ausgangspegel.
Falls Sie die Modulationslautstärke (Empfindlichkeit) einstellen möchten: Im Inneren des Mikrofons ist ein Empfindlichkeitsregler. (Einstell-Loch für Schraubendreher auf der Platine).
Ganz nach links gedreht = volle Empfindlichkeit, nach rechts gedreht wird das Mikro leiser.
Bitte benutzen Sie zur Kanalwahl nur die Tasten am Funkgerät

Important note: AE 4090 microphone

Dear Customer,
As a reaction to customer wishes we have modified the supplied microphone to a larger , heavy type with improved acoustical matching. The new microphone is better against wind and pop noise and has more output level. If You wish to adjust the output level: You will find a potentiometer inside the microphone (a hole for a screwdriver is in the middle of the PC board)
counterclockwise = full output, clockwise=less output.
For channel selection please use the keys on the radio.

ALAN Electronics GmbH